

Moisture-sensitive tablet & capsule containers



- Bottles produced in HDPE using injection blow molding for superior visual quality and dimensional accuracy;
- Available capacity: 35ml other capacities under development;
- Tamper-evident screw-on caps, with liner or desiccant capsule to suit product applications;
- Full batch documentation for each production order, with traceability of raw materials and products;
- Statistical batch-control and online checking during the production process supported by vision-measuring equipment;
- Food-grade raw materials, or according to the European Pharmacopeia;
- Produced and sealed in ISO Class 7 cleanroom with laminar flow ISO Class 5 according to ISO 14644;

We are certified to ISO 9001:2008 and ISO 15378:2011 standards, and all our operation is compliant with current GMP requirements concerning pharmaceutical primary packaging.

REFª	?	m		mm		IO
90100*	- Bottle	20	- HDPE	47~	40	- - - 36
90101		35		55	45	
90102*		50		64	46	
90149*		100		79	55	
90105	Cap Desic	n.a.	PP	23,5	42	
90120	Cap Liner	n.a.	PP	23,5	42	

*under development Subject to changes



